

Sizes

The Qseals QFWS18 is available in at least 4 different sizes:

D1	Unit
24.00	mm
42.00	mm
53.00	mm
75.00	mm

Technical specifications

Temperature	... till ... °C
Pressure	... bar
Rotational velocity	... m/s
Rotate left	No
Rotate right	No
Balanced	No

Alternatives

The Qseals QFWS18 is an alternative to at least 83 products of other brands:

- AES W06U
- Burgmann HRZ60
- Johnson C24-4511-02
- Johnson C24-4511-01
- Johnson C14-4514-06
- Johnson C14-4514-04 or 0A?
- Johnson C14-4514-03
- Johnson C14-4514-02
- Johnson C14-4514-01
- Johnson C14-4513-06
- Johnson C14-4513-04 or 0A?
- Johnson C14-4513-03
- Johnson C14-4513-01
- Johnson C14-4513-02
- Johnson C14-4512-06
- Johnson C14-4512-04 or 0A?
- Johnson C14-4512-03
- Johnson C14-4512-02
- Johnson C14-4512-01
- Johnson C14-4511-06
- Johnson C14-4511-04 or 0A?
- Johnson C14-4511-03
- Johnson C14-4511-02
- Johnson C14-4511-01
- Johnson C24-4511-03
- And 58 others...

Applications

The Qseals QFWS18 is used in at least 17 pumps and other applications:

- Hilge Domina S-?

- Johnson OnLine (OL)1/0004/15
- Johnson OnLine (OL)4/0324/07
- Johnson OnLine (OL)4/0243/10
- Johnson OnLine (OL)4/0162/15
- Johnson OnLine (OL)3/0108/07
- Johnson OnLine (OL)3/0081/10
- Johnson OnLine (OL)3/0054/15
- Johnson OnLine (OL)2/0034/07
- Johnson OnLine (OL)2/0025/10
- Johnson OnLine (OL)2/0017/15
- Johnson OnLine (OL)1/0008/07
- Johnson OnLine (OL)1/0006/10
- Viking Duralobe S1
- Viking Duralobe S2
- Viking Duralobe S3
- Viking Duralobe S4